

Project: Atlanta Hospital Test DJ - southwire
 Job: new dj.williams@southwire.com





(678) 877-9622

Reel Name:

Reel 9 N29C, 42 in, 1615 lbs





PULL 1 OF 9: 100 FT

From/To	gen / pnl
Metal/Insulation	CU THHN
Size	1/0
SIMpull™ Head	Yes

Colors		
Black		Red 
Blue		
White		





PULL 2 OF 9: 100 FT

From/To	gen / pnl
Metal/Insulation	CU THHN
Size	1/0
SIMpull™ Head	Yes

Colors		
Black		Red 
Blue		
White		





PULL 3 OF 9: 100 FT

From/To	gen / pnl
Metal/Insulation	CU THHN
Size	1/0
SIMpull™ Head	Yes

Colors		
Black		Red 
Blue		
White		





PULL 4 OF 9: 100 FT

From/To	gen / pnl
Metal/Insulation	CU THHN
Size	1/0
SIMpull™ Head	Yes

Colors		
Black		Red 
Blue		
White		




PULL 5 OF 9: 100 FT

From/To	gen / pnl
Metal/Insulation	CU THHN
Size	1/0
SIMpull™ Head	Yes

Colors		
Black		Red 
Blue		
White		




PULL 6 OF 9: 200 FT

	a / c
Metal/Insulation	AL THHN
Size	250
SIMpull™ Head	Yes

Colors					
Brown		Orange		Gray	




PULL 7 OF 9: 200 FT

From/To	a / c
Metal/Insulation	AL THHN
Size	250
SIMpull™ Head	Yes

Colors					
Brown		Orange		Gray	




PULL 8 OF 9: 200 FT

From/To	a / c
Metal/Insulation	AL THHN
Size	250
SIMpull™ Head	Yes

Colors					
Brown		Orange		Gray	

PULL 9 OF 9: 200 FT

From/To	a / c
Metal/Insulation	AL THHN
Size	250
SIMpull™ Head	Yes


Colors					
Brown		Orange		Gray	

Reel Name:

reel 10 N7, 30 in, 167 lbs

PULL 1 OF 5: 100 FT

From/To	gen / pnl
Metal/Insulation	CU THHN
Size	2
SIMpull™ Head	No

Colors			
Green			

PULL 2 OF 5: 100 FT

From/To	gen / pnl
Metal/Insulation	CU THHN
Size	2
SIMpull™ Head	No

Colors			
Green			

PULL 3 OF 5: 100 FT

	gen / pnl
Metal/Insulation	CU THHN
Size	2
SIMpull™ Head	No

Colors		
Green	<input checked="" type="radio"/>	

PULL 4 OF 5: 100 FT

	gen / pnl
Metal/Insulation	CU THHN
Size	2
SIMpull™ Head	No

Colors		
Green	<input checked="" type="radio"/>	

PULL 5 OF 5: 100 FT

	gen / pnl
Metal/Insulation	CU THHN
Size	2
SIMpull™ Head	No

Colors		
Green	<input checked="" type="radio"/>	

Reel Name:

reel 12 N7, 30 in, 188 lbs

PULL 1 OF 4: 200 FT

	a / c
Metal/Insulation	AL THHN
Size	2/0
SIMpull™ Head	No

Colors		
Green	<input checked="" type="radio"/>	

PULL 2 OF 4: 200 FT

	a / c
Metal/Insulation	AL THHN
Size	2/0
SIMpull™ Head	No

Colors		
Green	<input checked="" type="radio"/>	

PULL 3 OF 4: 200 FT

	a / c
Metal/Insulation	AL THHN
Size	2/0
SIMpull™ Head	No

Colors		
Green	<input checked="" type="radio"/>	

PULL 4 OF 4: 200 FT



	a / c
Metal/Insulation	AL THHN
Size	2/0
SIMpull™ Head	No

Colors		
Green	<input checked="" type="radio"/>	
	<input type="radio"/>	



CONDUCTORS SUMMARY (DETAILED)

Metal	Insulation	Color	Size	Length (ft)	Weight (lb)
AL	SIMpull™ THHN	Green	2/0	800	137
AL	SIMpull™ THHN	Brown	250	800	248
AL	SIMpull™ THHN	Orange	250	800	248
AL	SIMpull™ THHN	Gray	250	800	249
CU	SIMpull™ THHN	Green	2	500	117
CU	SIMpull™ THHN	Black	1/0	500	186
CU	SIMpull™ THHN	Red	1/0	500	186
CU	SIMpull™ THHN	Blue	1/0	500	186
CU	SIMpull™ THHN	White	1/0	500	186

CONDUCTORS SUMMARY (TOTALS ONLY)

Metal	Insulation	Size	Length (ft)	Weight (lb)
AL	SIMpull™ THHN	2/0	800	137
AL	SIMpull™ THHN	250	2400	747
CU	SIMpull™ THHN	2	500	117



CU	SIMpul™ THHN	1/0	2000	744
----	--------------	-----	------	-----

AL			3200	884
CU			2500	861